



TECHSPEC® Negative Achromatic Lenses

Edmund Optics Inc.

USA | UK | France | Germany | Japan | Singapore | China | Korea | Italy

TECHSPEC® NEGATIVE ACHROMATIC LENSES




62478INK
TUE DEC 16 2008 UNITS ARE μm .
FIELD :
RMS RADIUS : 51.276
GD RADIUS : 67.647
SCALE BAR : 200

REFERENCE : CHIEF RAY

EDMUND OPTICS
HTTP://WWW.EDMUNDOPTICS.COM

62478INK
TUE DEC 16 2008
MAXIMUM FOCAL SHIFT RANGE: 34.9740 μm
DIFFRACTION LIMITED RANGE: 6.979 μm
PUPIL ZONE: 0.0000

EDMUND OPTICS
HTTP://WWW.EDMUNDOPTICS.COM



TRANSVERSE RAY FAN PLOT

62478INK
TUE DEC 16 2008
MAXIMUM SCALE: $\pm 100.000 \mu\text{m}$.
0.486 0.588 0.656


SURFACE: IMAGE

EDMUND OPTICS
HTTP://WWW.EDMUNDOPTICS.COM

62478INK
TUE DEC 16 2008
DATA FOR 0.4250 TO 0.6750 μm .
SURFACE: IMAGE

POLYCHROMATIC DIFFRACTION MTF

EDMUND OPTICS
HTTP://WWW.EDMUNDOPTICS.COM



EO Edmund
optics | worldwide

www.edmundoptics.com