





FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING



LONGPASS FILTER

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

REV. 001	S1	S2
SHAPE	PLANO	PLANO
SPECTRAL TRANSMITTANCE $t_p(\%)$	93	93
PASSBAND LIMIT 1 λ_{p1} (nm)	620	620
CUT-OFF POSITION λ_c (nm)	600±6	600±6
STOPBAND LIMIT λ_s (nm)	558	558
WAVELENGTH	VIS	VIS
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED



ALL DIMS IN

mm

TITLE

Ø25.4mm, HOYA R-60 LONGPASS FILTER

DWG NO

66054

SHEET
1 OF 1