





**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**



	VALUE
OPTICAL DENSITY	≥4.0
CENTER WAVELENGTH (CWL)	1000 ±2 nm
FULL WIDTH HALF MAX (FWHM)	12 ±2 nm
MINIMUM TRANSMISSION	>70 %
BLOCKING	200 - 1200nm
SURFACE QUALITY	80-50
CONSTRUCTION	MOUNTED IN BLACK ANODIZED RING
COATING TYPE	TRADITIONAL COATED

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY



TITLE	Ø25mm, 1000nm x 10nm, MOUNTED BANDPASS FILTER		
DWG NO	65782	SHEET	1 OF 1

ALL DIMS IN

mm