

NOTES:


1. SUBSTRATE: Float Glass
2. COATING (APPLY ACROSS CLEAR APERTURE)

S1: Protected Gold (700-10000nm)

R(AVG) >96% @ 700 - 2000nm

R(AVG) >96% @ 2000 - 10,000nm

S2: NONE
3. EDGES GROUND
4. ROHS COMPLIANT



**FOR INFORMATION ONLY:**  
**DO NOT MANUFACTURE**  
**PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

|                  | S1                  | S2                  |
|------------------|---------------------|---------------------|
| SHAPE            | PLANO               | PLANO               |
| SURFACE QUALITY  | 60-40               | N/A                 |
| SURFACE FLATNESS | 4 - 6λ              | N/A                 |
| CLEAR APERTURE   | Ø 14.00             | N/A                 |
| BEVEL            | PROTECTED AS NEEDED | PROTECTED AS NEEDED |

THIRD ANGLE  
PROJECTION

Edmund Optics®

TITLE

15mm Dia Protected Gold, 4-6λ Mirror

ALL DIMS IN

mm

DWG NO

43731

SHEET  
1 OF 1