NOTES:

1. SUBSTRATE MATERIAL: FLOAT GLASS


2. ROHS COMPLIANT


3. COATING (APPLY ACROSS CLEAR APERTURE)

S1: 40% R ±5% @ 550nm 60% T ±5% @ 550nm

S2: AR ¼λ MgF2 @ 550nm







FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS ARE FOR REFERENCE ONLY

REV. A	\$1	\$2
SHAPE	PLANO	PLANO
SURFACE QUALITY	80-50	80-50
SURFACE FLATNESS	4 - 6λ	4 - 6λ
BEVEL	PROTECTED AS NEEDED	PROTECTED AS NEEDED

	THIRD ANGLE PROJECTION	$\phi \Box$	Т
)	ALL DIMS IN	mm	D

	Edmund Optic	S®
тітье 127	x 178mm, 40 R/60 T, PLATE BEAMSPLITTER	
DWG NO	61260	SHEET 1 OF 1