




NOTES:


1. SUBSTRATE: AS87ECO
2. COATING (APPLY ACROSS CLEAR APERTURE):  
S1 & S2: NONE
3. ROHS: COMPLIANT



**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2
SHAPE	PLANO	PLANO
SURFACE QUALITY	80-50	80-50
SURFACE ROUGHNESS	< 0.50	< 0.50
CLEAR APERTURE	9.00 x 9.00	9.00 x 9.00
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED

THIRD ANGLE PROJECTION 

ALL DIMS IN mm

 **Edmund Optics®**

TITLE: 10 x 10mm, 0.1mm THICK, SCHOTT AS87ECO  
ULTRA-THIN WINDOW

DWG NO: 12292

SHEET 1 OF 1