


NOTES:

1. SUBSTRATE: AS87ECO
2. COATING (APPLY ACROSS CLEAR APERTURE):
S1 & S2: NONE
3. ROHS: COMPLIANT



FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
 DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2
SHAPE	PLANO	PLANO
SURFACE QUALITY	80-50	80-50
SURFACE ROUGHNESS	< 0.50	< 0.50
CLEAR APERTURE	11.43 x 22.86	11.43 x 22.86
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED



ALL DIMS IN mm



TITLE

12.7 x 25.4mm, 0.1mm THICK, SCHOTT
 AS87ECO ULTRA-THIN WINDOW

DWG NO

12298

SHEET
 1 OF 1