







FOCAL LENGTH (EFL): $19,1 \pm 0,19$
 BACK FOCAL LENGTH (BFL): $15,38$

1 BLACKENED SURFACE

SURFACE A			SURFACE B		SURFACE C		
Øe 11,7			Øe 11,7		Øe 11,7		
			CEMENT: NOA 61 OR EQUIVALENT				
PROTECTIVE CHAMFERS AS NEEDED			FIRST ANGLE PROJECTION 	 Edmund Optics® TITLE12,7mm Dia, x 19,1mm FL, VIS-NIR, Inked, Achromatic Lens			
ROHS: COMPLIANT	SCALE: NONE	λ = 587,6nm					
SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY				DWG NO49785INK			
FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING							
INDICATIONS IN ACCORDANCE WITH ISO 10110			ALL DIMS IN:	mm	SHEET SIZE A4		SHEET 1 OF 3



- 1 AR COATING: VIS-NIR
 $R(ABS) \leq 0,25\%$ AT 880nm @ 0° AOI
 $R(AVG) \leq 1,25\%$ FROM 400-870nm @ 0° AOI
 $R(AVG) \leq 1,25\%$ FROM 890-1000nm @ 0° AOI

LEFT SURFACE	MATERIAL	RIGHT SURFACE
R 13,185±0,013 CX Øe 11,7 3/ 3 (0,5) λ=632,8 nm 4/ - 5/ 40 - 20 (MIL-PRF-13830B) 6/ -	GLASS N-BaF10 670/472	R 10,215±0,01 CX Øe 11,7 3/ 3 (0,5) λ=632,8 nm 4/ - 5/ 40 - 20 (MIL-PRF-13830B) 6/ -

PROTECTIVE CHAMFERS AS NEEDED


ROHS: COMPLIANT SCALE: NONE λ = 587,6nm

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY

FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING

INDICATIONS IN ACCORDANCE WITH ISO 10110

FIRST ANGLE PROJECTION




ALL DIMS IN: mm

EO® Edmund Optics®

TITLE 12,7mm Dia, x 19,1mm FL, VIS-NIR, Inked, Achromatic Lens

DWG NO 497851NK

SHEET SIZE A4 SHEET 2 OF 3



- 1 AR COATING: VIS-NIR
 $R(ABS) \leq 0,25\%$ AT 880nm @ 0° AOI
 $R(AVG) \leq 1,25\%$ FROM 400-870nm @ 0° AOI
 $R(AVG) \leq 1,25\%$ FROM 890-1000nm @ 0° AOI

LEFT SURFACE	MATERIAL	RIGHT SURFACE
R 10,215±0,01 CV Øe 11,7 3/ 3 (0,5) λ=632,8 nm 4/ - 5/ 40 - 20 (MIL-PRF-13830B) 6/ -	GLASS N-SF6 805/254	R 50,875±0,051 CX Øe 11,7 3/ 3 (0,5) λ=632,8 nm 4/ - 5/ 40 - 20 (MIL-PRF-13830B) 6/ -

PROTECTIVE CHAMFERS AS NEEDED

ROHS:
COMPLIANT

SCALE:
NONE

λ = 587,6nm

FIRST ANGLE
PROJECTION



Edmund Optics®

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT
NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY

FOR INFORMATION ONLY: DO NOT MANUFACTURE
PARTS TO THIS DRAWING

INDICATIONS IN ACCORDANCE WITH ISO 10110

ALL DIMS
IN:

mm

TITLE

12,7mm Dia, x 19,1mm FL, VIS-NIR,
Inked, Achromatic Lens

DWG NO

497851NK

SHEET SIZE
A4

SHEET
3 OF 3