



NOTES:

- 1. SUBSTRATE: SCHOTT GG400
- 2. SURFACE S2 TO BE PARALLEL TO SURFACE S1 TO WITHIN 1 ARCMIN

**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**




SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

	VALUE
SHAPE	PLANO
CUT-ON WAVELENGTH (nm)	400 ±6
PASSBAND LIMIT 1 (nm)	480
STOPBAND LIMIT (nm)	340
SURFACE QUALITY	60-40
CLEAR APERTURE	48.50 x 48.50
BEVEL MAX FACE	PROTECTIVE AS NEEDED

THIRD ANGLE
PROJECTION

ALL DIMS IN

mm

 **Edmund Optics®**

TITLE	SCHOTT GG400 50 x 50mm COLORED LONGPASS FILTER, 2mm THK		
DWG NO	14476	SHEET 1 OF 1	