




**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**



SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

DIFFUSING ANGLE (°)	45 x 35 (FWHM)
OPERATING TEMPERATURE (°C)	-30 to +100 (Maximum of 240 Hours)
SUBSTRATE	Polycarbonate
TRANSMISSION (%)	>85
RoHS	COMPLIANT



THIRD ANGLE  
PROJECTION

ALL DIMS IN

mm

**EO<sup>®</sup> Edmund Optics<sup>®</sup>**

TITLE

45 x 35° Diffusing Angle, 25mm Dia, Mounted  
Flat Top Holographic Diffuser

DWG NO

15831

SHEET  
1 OF 1