




**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**



SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

DIFFUSING ANGLE (°)	45 x 35 (FWHM)
OPERATING TEMPERATURE (°C)	-30 to +100 (Maximum of 240 Hours)
SUBSTRATE	Polycarbonate
TRANSMISSION (%)	>85
RoHS	COMPLIANT

THIRD ANGLE
PROJECTION

ALL DIMS IN

mm

 Edmund Optics®			
TITLE		45 x 35° Diffusing Angle, 50mm Dia., Mounted Flat Top Holographic Diffuser	
DWG NO		15832	SHEET 1 OF 1