




1. SUBSTRATE:  
SCHOTT KG1
2. COATING (APPLY ACROSS CLEAR APERTURE)  
S1 & S2: NONE

### 3. FINE GRIND SURFACE

4. DENSITY (g/cm³): 2.53  
OPERATING TEMPERATURE (°C): 300 Maximum  
REFLECTION FACTOR: 0.92


## 5. ROHS COMPLIANT



**FOR INFORMATION ONLY:**  
**DO NOT MANUFACTURE**  
**PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY



	S1	S2	<div>THIRD ANGLE PROJECTION</div> 		TITLE	SCHOTT KG1, 12.5mm Dia., 2mm Thick, Colored Glass Heat Absorbing Shortpass Filter	
SHAPE	PLANO	PLANO					
SURFACE QUALITY	60-40	60-40					
BEVEL	PROTECTED AS NEEDED	PROTECTED AS NEEDED	ALL DIMS IN	mm	DWG NO	18496	SHEET 1 OF 1