




- NOTES:
- 1. SUBSTRATE:
SCHOTT KG2
 - 2. COATING (APPLY ACROSS CLEAR APERTURE)
S1 & S2: NONE

3. FINE GRIND SURFACE

- 4. DENSITY (g/cm³): 2.52
OPERATING TEMPERATURE (°C): 300 Maximum
REFLECTION FACTOR: 0.92
- 5. ROHS COMPLIANT



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

EO® **Edmund Optics®**

	S1	S2	THIRD ANGLE PROJECTION		TITLE	SCHOTT KG2, 12.5mm Dia., 2mm Thick, Colored Glass Heat Absorbing Shortpass Filter	
SHAPE	PLANO	PLANO					
SURFACE QUALITY	60-40	60-40	ALL DIMS IN	mm	DWG NO	18498	SHEET 1 OF 1
BEVEL	PROTECTED AS NEEDED	PROTECTED AS NEEDED					