




- NOTES:
- 1. SUBSTRATE:
AS87ECO
 - 2. COATING (APPLY ACROSS CLEAR APERTURE)

S1 & S2: NONE
 - 3. ROHS COMPLIANT



FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2
SHAPE	PLANO	PLANO
SURFACE QUALITY	80-50	80-50
SURFACE ROUGHNESS	< 0.50nm	< 0.50nm
CLEAR APERTURE	Ø 36.00	Ø 36.00
BEVEL	PROTECTED AS NEEDED	PROTECTED AS NEEDED

EO® Edmund Optics®



THIRD ANGLE
PROJECTION

TITLE

SCHOTT AS87ECO, 40mm Dia., 0.1mm Thick,
Ultra-Thin Window

ALL DIMS IN

mm

DWG NO

20214

SHEET
1 OF 1