





FOCAL LENGTH (EFL): 50 ±0,5  
 BACK FOCAL LENGTH (BFL): 46,17

- 1 532nm V-COAT  
 R(ABS) < 0,25% @ 532nm @ 0° AOI

| LEFT SURFACE                                                                             |                |             | MATERIAL                                                                            | RIGHT SURFACE                                                                                                                      |        |                 |
|------------------------------------------------------------------------------------------|----------------|-------------|-------------------------------------------------------------------------------------|------------------------------------------------------------------------------------------------------------------------------------|--------|-----------------|
| R 33,63 CX                                                                               |                |             | GLASS N-SF5 673/322<br>Nd: 1,673<br>Vd: 32,25                                       | R ∞ PL                                                                                                                             |        |                 |
| Øe 29                                                                                    |                |             |                                                                                     | Øe 29                                                                                                                              |        |                 |
| ⌀ SEE NOTE 1                                                                             |                |             |                                                                                     | ⌀ SEE NOTE 1                                                                                                                       |        |                 |
| 3/ 3 (0,5) λ=632,8 nm                                                                    |                |             |                                                                                     | 3/ 3 (0,5) λ=632,8 nm                                                                                                              |        |                 |
| 4/ -                                                                                     |                |             |                                                                                     | 4/ 1,49'                                                                                                                           |        |                 |
| 5/ 40 - 20                                                                               |                |             |                                                                                     | 5/ 40 - 20                                                                                                                         |        |                 |
| 6/ -                                                                                     |                |             | 6/ -                                                                                |                                                                                                                                    |        |                 |
| PROTECTIVE CHAMFERS AS NEEDED                                                            |                |             | FIRST ANGLE<br>PROJECTION                                                           | <div><div></div><div>Edmund Optics®</div></div> |        |                 |
| ROHS:<br>COMPLIANT                                                                       | SCALE:<br>NONE | λ = 587,6nm |                                                                                     |                                                                                                                                    |        |                 |
| SPECIFICATIONS SUBJECT TO CHANGE<br>WITHOUT NOTICE. DIMENSIONS ARE FOR<br>REFERENCE ONLY |                |             |  | TITLE<br>30mm Dia x 50mm FL, 532nm V-Coat<br>Coated, Plano-Convex Lens                                                             |        |                 |
| FOR INFORMATION ONLY: DO NOT<br>MANUFACTURE PARTS TO THIS DRAWING                        |                |             |                                                                                     |                                                                                                                                    |        |                 |
| INDICATIONS IN ACCORDANCE WITH ISO 10110                                                 |                |             | ALL<br>DIMS IN:                                                                     | mm                                                                                                                                 | DWG NO | 26134           |
|                                                                                          |                |             | SHEET<br>T SIZE                                                                     |                                                                                                                                    |        | A4              |
|                                                                                          |                |             |                                                                                     |                                                                                                                                    |        | SHEET<br>1 OF 1 |