

[Alle Produkte](#) / [Optikkomponenten](#) / [Fenster und Diffusoren](#) / [Spezialfenster](#)

TECHSPEC® Keilfenster aus N-BK7 Mehr Produkte von [SCHOTT Optical Components](#)



- N-BK7-Substrate mit Keilwinkel von 30 Bogenminuten
- $\lambda/10$ Oberflächenebenheit und Oberflächenqualität 20-10
- Ideal für die Eliminierung von Etalon-Effekten
- [Keilfenster aus Quarzglas](#) und [plane Fenster aus N-BK7](#) sind ebenfalls verfügbar

Spezifikationen

Physikalische und mechanische Eigenschaften

Dicke (mm):	3.00 ±0.20	Kanten:	Fine Ground
Elastizitätsmodul (GPa):	82		

Optische Eigenschaften

Brechungsindex (n_d):	1.516		
Substrat:	N-BK7	Oberflächenqualität:	20-10

Technische Informationen

Produkte

Durchm. (mm)	Dicke (mm)	Beschichtung	Kanten	Substrat	Artikelnummer	Preis	Kaufen
12.50	3.00	Uncoated	Fine Ground	N-BK7	#34-244	€95,79 Mengenrabatte	8 In Stock
12.50	3.00	VIS-EXT (350- 700nm)	Fine Ground	N-BK7	#25-624	€122,57 Mengenrabatte	Kontakt
12.50	3.00	VIS-NIR (400- 1000nm)	Fine Ground	N-BK7	#25-724	€122,57 Mengenrabatte	1 In Stock
25.00	3.00	Uncoated	Fine Ground	N-BK7	#34-245	€127,72 Mengenrabatte	2 In Stock
25.00	3.00	VIS-EXT (350- 700nm)	Fine Ground	N-BK7	#25-625	€154,50 Mengenrabatte	1 In Stock
25.00	3.00	VIS-NIR (400- 1000nm)	Fine Ground	N-BK7	#25-725	€154,50 Mengenrabatte	1 In Stock
50.00	3.00	Uncoated	Fine Ground	N-BK7	#34-246	€188,49 Mengenrabatte	15 In Stock
50.00	3.00	VIS-EXT (350- 700nm)	Fine Ground	N-BK7	#25-626	€223,51 Mengenrabatte	3 In Stock
50.00	3.00	VIS-NIR (400- 1000nm)	Fine Ground	N-BK7	#25-726	€223,51 Mengenrabatte	7 In Stock



Copyright 2023 | Edmund Optics, Ltd Unit 1, Opus Avenue, Nether Poppleton, York, YO26 6BL, UK

Telefonnr.: 1-800-363-1992 :

www.edmundoptics.com