

0 - 0.5", Quick Mini Digital Thickness Gage

Mehr Produkte von [Mitutoyo](#)



Produkt **#78-359** **1 In Stock**

-

1

+

€216⁰⁰

+ WARENKORB

Mengenrabatte	
Stk. 1+	€216,00 stückpreis
Need More?	Angebotsanfrage

 Preise exklusiv der geltenden Mehrwertsteuer und Abgaben

Downloadbereich

SPEZIFIKATIONEN

Produktdetails

0 - 0.50 inches

Bereich:

700-118-30

Modellnummer:

±0.001	Genauigkeit (Zoll):
Physikalische und mechanische Eigenschaften	
0.0005	Auflösung (Zoll):
Konformität mit Standards	
Anzeigen	Konformitätszertifikat:

PRODUKTDDETAILS

- 0 – 0.5" Range with 0.0005" Resolution
- Easy-To-Read Digital LCD Display
- ABSOLUTE® Linear Scale Eliminates Need for Zeroing

Mitutoyo Thickness Gauges are designed to quickly measure the thickness of different materials or objects with high accuracy of ±0.001". An ABSOLUTE® linear scale eliminates the need for setting the origin point everytime the gauge is powered on and prevents over speed errors. These thickness gauges feature ceramic spindles and anvils for high corrosion resistance and waterproof data output connectors to protect against dust, water, and oil ingress. Mitutoyo Thickness Gauges are ideal for quick inspection of a wide range of materials and objects including paper, film, wire, sheet metal, leather, and plastic parts. The grip handle, easy-to-reach lifting lever, spring-loaded spindle, and LCD display allow for quick, easy, and accurate measurements.