

Optikhalterung für den schnellen Aufbau, Filterhalterung für mehrere Filter, 30 mm Durchmesser



#55-006



Produkt **#17-532** AUSVERKAUF KONTAKT

-

1

+

€153^{.75}

+ WARENKORB

Mengenrabatte	
Stk. 1+	€153,75 stückpreis
Need More?	Angebotsanfrage

i Preise exklusiv der geltenden Mehrwertsteuer und Abgaben

Downloadbereich

Produktdetails	
Fixed	Typ:
Circular	Optiktyp:
Inhalt des Sets:	

Physikalische und mechanische Eigenschaften		
Black Anodized Aluminum		Aufbau:
5.0		Max. Dicke der kompatiblen Optiken (mm):
127.00		Höhe optische Achse (mm):
25.4		Stangendurchmesser (mm):
Gewinde & Montage		
30.0		Größe der kompatiblen Optiken (mm):
M6 x 1.0		Kompatible Stangen:

Konformität mit Standards		
Konform		RoHS 2015:
Anzeigen		Konformitätszertifikat:
Konform		Reach 233:

Produktdetails

- Übliche Höhe der optischen Achse von 5" (127 mm) für einfache Systemintegration
- Optische Halterungen und Stangen mit Standfuß als Paket mit 5% Rabatt
- Ideal für den Neuaufbau von Optiksystemen im Labor

Die Optikhalterungen für den schnellen Aufbau haben eine einheitliche Achsenhöhe von 5" (127 mm) zur Tischoberfläche und kombinieren die gesamten benötigten Komponenten für eine einfache Systemintegration. Die Halterungen passen zu einer Vielzahl an optischen Komponenten, komplexen Systemen und Experimenten und können ohne eine aufwendige Ausrichtung der optischen Achse einfach aufgebaut werden. Mit den Optikhalterungen für den schnellen Aufbau können unter Einsatz der bekannten Halterungen von Edmund Optics wie den kinematischen optischen Spiegelhalterungen der E-Serie, den TECHSPEC kinematischen optischen Spiegelhalterungen, den kompakten Spiegel- & Linsenhalterungen sowie den Halterungen für optische Komponenten einfach und zeitsparend neue optische Systeme im Labor aufgebaut werden.

Technische Informationen

Kit Stock No.	Kit Description	Contents of Kit
#17-513	25.0/25.4mm Optic Diameter, X-Y Translating Quick Start Optical Mounts	#62-956: 25.0/25.4mm Optic Dia., X-Y Translating Optic Mount #16-460: Pedestal Extender 20.8mm, M6, 8-32 #15-849: Pedestal Post, English, 76.2mm
#17-514	50.0/50.8mm Optic Diameter, X-Y Translating Optic Mount, Quick Start Optical Mounts	#62-957: 50.0/50.8mm Optic Dia., X-Y Translating Optic Mount #16-317: Pedestal Extender 8.0mm, 8-32, M6 #15-849: Pedestal Post, English, 76.2mm
#17-515	25.4mm Optic Dia., Fixed Optic Mount, Quick Start Optical Mounts	#64-561: 25.4mm Optic Dia., 10mm Max Optic Thickness, Optic Mount #16-305: Pedestal Shim 5/32" (3.97mm) #16-333: 12.5mm Length 1/4"-20, #8-32 Thread Adapter #15-850: Pedestal Post, English, 101.6mm
#17-516	50.0mm Optic Dia., Fixed Optic Mount, Quick Start Optical Mounts	#64-567: 50.0mm Optic Dia., Optic Mount #16-321: Pedestal Extender 16.8mm, 8-32, M6 #15-849: Pedestal Post, English, 76.2mm
#17-517	25/25.4mm ID, Precision Gimbal Mount, Quick Start Optical Mounts	#54-999: 25.0/25.4mm Optic Dia., Precision Gimbal Mount #16-308: Pedestal Shim 1/16" (1.59mm) #16-329: 10.5mm Length M6, #8-32 Thread Adapter #15-849: Pedestal Post, English, 76.2mm
#17-518	50/50.8mm ID, Precision Gimbal Mount, Quick Start Optical Mounts	#55-000: 50.0/50.8mm Optic Dia., Precision Gimbal Mount #16-310: Pedestal Shim 1/64" (0.40mm) #16-321: Pedestal Extender 16.8mm, 8-32, M6 #15-848: Pedestal Post, English, 50.8mm
#17-519	25.0/25.4mm Optic Dia., Kinematic Mirror Mount with Micrometer, Quick Start Optical Mounts	#55-456: 25.0/25.4mm Optic Dia., Kinematic Mirror Mount with Micrometer #16-319: Pedestal Extender 14.0mm, 8-32, M6 #16-309: Pedestal Shim 1/32" (0.79mm) #15-849: Pedestal Post, English, 76.2mm
#17-520	50.0/50.8mm Optic Dia., Kinematic Mirror Mount with Micrometer, Quick Start Optical Mounts	#56-326: 50.0/50.8mm Optic Dia., Kinematic Mirror Mount with Micrometer #16-304: Pedestal Shim 3/16" (4.76mm) #16-331: 15.0mm Length M6, #8-32 Thread Adapter #15-849: Pedestal Post, English, 76.2mm
#17-521	25/25.4mm Diameter, E-Series Kinematic Mount, Quick Start Optical Mounts	#15-866: 25.0/25.4mm Optic Dia., E-Series Kinematic Mount #15-850: Pedestal Post, English, 101.6mm
#17-522	50/50.8mm Diameter, E-Series Kinematic Mount, Quick Start Optical Mounts	#15-867: 50.0/50.8mm Optic Dia., E-Series Kinematic Mount #15-857: Pedestal Extender, English, 76.2mm #15-845: Pedestal Post, English, 12.7mm

#17-523	25/25.4mm Dia., Kinematic Mount, 3-Screws, Quick Start Optical Mounts	#58-854 : 25.0/25.4mm Optic Dia., Kinematic Mount, 3-Screws #15-850 : Pedestal Post, English, 101.6mm
#17-524	50/50.8mm Dia., Kinematic Mount, 3-Screws, Quick Start Optical Mounts	#58-855 : 50.0/50.8mm Optic Dia., Kinematic Mount, 3-Screws #15-857 : Pedestal Extender, English, 76.2mm #15-845 : Pedestal Post, English, 12.7mm
#17-525	25.4mm w/ micrometer, Polarizer Mount, Quick Start Optical Mounts	#55-011 : 25.4mm w/ micrometer, Polarizer Mount #16-322 : Pedestal Extender 18.0mm, 8-32, M6 #15-849 : Pedestal Post, English, 76.2mm
#17-526	50.0mm w/ micrometer, Polarizer Mount, Quick Start Optical Mounts	#56-329 : 50.0mm w/ micrometer, Polarizer Mount #16-317 : Pedestal Extender 8.0mm, 8-32, M6 #15-849 : Pedestal Post, English, 76.2mm
#17-527	50mm Cube, Prism Mount Metric, Quick Start Optical Mounts	#55-013 : 50mm Diameter, Prism Mount Metric #16-322 : Pedestal Extender 18.0mm, 8-32, M6 #16-309 : Pedestal Shim 1/32" (0.79mm) #15-848 : Pedestal Post, English, 50.8mm
#17-528	50mm Cube Rotary Mount with Prism Holder, Quick Start Optical Mounts	#53-027 : Rotary Mount with Prism Holder #16-325 : Pedestal Extender 18.0mm, 8-32, 1/4"-20 #15-848 : Pedestal Post, English, 50.8mm
#17-529	2"/50.8mm Square, Bar Clamp, Quick Start Optical Mounts	#54-995 : 60mm sq - Rectangular Bar Clamp #16-318 : Pedestal Extender 11.0mm, 8-32, M6 #15-849 : Pedestal Post, English, 76.2mm
#17-530	2"/50.8mm Diameter, Bar Type Lens / Filter Holder, Quick Start Optical Mounts	#03-669 : 7.0 - 67.0 Optic Height, English Bar-Type Optic Holder #16-323 : Pedestal Extender 11.0mm, 8-32, 1/4"-20 #15-849 : Pedestal Post, English, 76.2mm
#17-531	2"/50.8mm Square, Spring Mount Filter Holder, Quick Start Optical Mounts	#55-531 : Spring Mount Filter Holder, Metric #16-320 : Pedestal Extender 16.0mm, 8-32, M6 #15-849 : Pedestal Post, English, 76.2mm
#17-532	30mm Dia., Multiple Filter Holder, Quick Start Optical Mounts	#55-006 : 30mm, Multiple Filter Holder #16-321 : Pedestal Extender 16.8mm, 8-32, M6 #15-849 : Pedestal Post, English, 76.2mm
#17-533	25mm Dia., Manual Filter Wheel, Quick Start Optical Mounts	#34-545 : Manual Cage Filter Wheel #16-329 : 10.5mm Length M6, #8-32 Thread Adapter #15-850 : Pedestal Post, English, 101.6mm
#17-534	25.4mm Optic Dia., Thin Mirror Mount, M4, Quick Start Optical Mounts	#13-590 : 25.4mm Optic Dia., Thin Mirror Mount M4 #15-844 : Pedestal Post, Metric, 101.6mm
#17-535	25.4mm Optic Dia., Thin Mirror Mount, 8-32, Quick Start Optical Mounts	#13-591 : 25.4mm Optic Dia., Thin Mirror Mount, 8-32 #15-850 : Pedestal Post, English, 101.6mm
#17-536	25.0/25.4mm Optic Dia., SM1 Thin Mount, M4, Quick Start Optical Mounts	#13-787 : 25.0/25.4mm Optic Dia., SM1 Thin Mount, M4 #15-844 : Pedestal Post, Metric, 101.6mm
#17-537	25.0/25.4mm Optic Dia., SM1 Thin Mount, 8-32, Quick Start Optical Mounts	#13-788 : 25.0/25.4mm Optic Dia., SM1 Thin Mount, 8-32 #15-850 : Pedestal Post, English, 101.6mm