

Irisblende mit Nullapertur, 37 mm maximale Apertur



Produkt **#53-908** 4 In Stock

-

1

+

€82⁵⁰

+ WARENKORB

Mengenrabatte	
Stk. 1-9	€82,50 stückpreis
Stk. 10-25	€72,90 stückpreis
Stk. 26+	€67,40 stückpreis
Need More?	Angebotsanfrage

i Preise exklusiv der geltenden Mehrwertsteuer und Abgaben

Downloadbereich

Produktdetails

Unmounted

Typ:

Physikalische und mechanische Eigenschaften

Max. Apertur (mm):

Außendurchm. A	Max. Apertur B	Min. Apertur C	Dicke D	Produktnr.
102mm	75mm	0mm	9.1mm	#64-506
21mm	12mm		6.2mm	#53-906
29mm	12mm		6.1mm	#62-649
38mm	25mm			#53-907
54mm	37mm		7.5mm	#53-908
72mm	50mm		9.1mm	#53-909
37mm	12mm		6.2mm	#62-653
54mm	25mm		6.1mm	#62-654
67mm	37mm		7.5mm	#62-655
88mm	50mm		9.1mm	#62-656

Zero Aperture Series Iris Diaphragms

The diagram illustrates the Zero Aperture Series Iris Diaphragm. The front view (left) shows a circular diaphragm with a central iris mechanism. The outer diameter is labeled A, the maximum aperture is B, and the minimum aperture is C. The side view (right) shows the thickness of the diaphragm, labeled D, and the lever actuator mechanism. The units are specified as mm.

Units: mm

