

[Alle Produkte](#) / [Optomechanik](#) / [Optomechanik-Blenden](#) / [Lochblenden oder Spaltblenden](#)

Geschwärzte Lochblenden von Acktar

Mehr Produkte von [Acktar](#)



- Geringer Reflexionsgrad vom EUV bis SWIR
- Schwarze Beschichtung mit einem Absorptionsgrad von 99%
- Aperturgrößen von 20 bis 1000 µm
- Gefasste und ungefasste Versionen verfügbar

Spezifikationen

Physikalische und mechanische Eigenschaften

Aufbau: Stainless Steel

Materialeigenschaften

Absorption (%): 99

Technische Informationen

Produkte

Typ	Außendurchmesser (mm)	Aufbau	Fester Aperturdurchmesser (µm)	Artikelnummer	Preis	Kaufen
Unmounted	9.53	Stainless Steel	20	#15-386	€145,23 Mengenrabatte	3 In Stock
Unmounted	9.53	Stainless Steel	25	#15-387	€145,23 Mengenrabatte	2 In Stock
Unmounted	9.53	Stainless Steel	50	#12-166	€145,23 Mengenrabatte	1 In Stock
Unmounted	9.53	Stainless Steel	75	#15-388	€145,23 Mengenrabatte	2 In Stock
Unmounted	9.53	Stainless Steel	100	#12-167	€145,23 Mengenrabatte	5 In Stock
Unmounted	9.53	Stainless Steel	150	#15-389	€145,23 Mengenrabatte	4 In Stock
Unmounted	9.53	Stainless Steel	200	#12-168	€145,23 Mengenrabatte	5 In Stock
Unmounted	9.53	Stainless Steel	300	#15-390	€145,23 Mengenrabatte	2 In Stock
Unmounted	9.53	Stainless Steel	400	#15-391	€145,23 Mengenrabatte	Kontakt
Unmounted	9.53	Stainless Steel	500	#12-169	€145,23 Mengenrabatte	4 In Stock
Unmounted	9.53	Stainless Steel	600	#15-392	€145,23 Mengenrabatte	8 In Stock
Unmounted	9.53	Stainless Steel	800	#16-738	€145,23 Mengenrabatte	4 In Stock
Unmounted	9.53	Stainless Steel	1000	#12-170	€145,23 Mengenrabatte	5 In Stock
Mounted	12.7	Stainless Steel	25	#16-821	€155,53 Mengenrabatte	3 In Stock
Mounted	12.7	Stainless Steel	50	#16-822	€155,53 Mengenrabatte	20+ In Stock
Mounted	12.7	Stainless Steel	75	#16-823	€155,53 Mengenrabatte	20+ In Stock
Mounted	12.7	Stainless Steel	100	#16-824	€155,53 Mengenrabatte	2 In Stock
Mounted	12.7	Stainless Steel	150	#16-825	€155,53 Mengenrabatte	1 In Stock
Mounted	12.7	Stainless Steel	200	#16-826	€155,53 Mengenrabatte	3 In Stock

Mounted	12.7	Stainless Steel	300	#16-827	€155,53 Mengenrabatte	4 In Stock
Mounted	12.7	Stainless Steel	500	#16-828	€155,53 Mengenrabatte	5 In Stock
Mounted	12.7	Stainless Steel	1000	#16-829	€155,53 Mengenrabatte	Kontakt
Mounted	25.0	Stainless Steel	20	#15-393	€155,53 Mengenrabatte	4 In Stock
Mounted	25.0	Stainless Steel	25	#15-394	€155,53 Mengenrabatte	5 In Stock
Mounted	25.0	Stainless Steel	50	#12-171	€155,53 Mengenrabatte	5 In Stock
Mounted	25.0	Stainless Steel	75	#15-395	€155,53 Mengenrabatte	3 In Stock
Mounted	25.0	Stainless Steel	100	#12-172	€155,53 Mengenrabatte	6 In Stock
Mounted	25.0	Stainless Steel	150	#15-396	€155,53 Mengenrabatte	4 In Stock
Mounted	25.0	Stainless Steel	200	#12-173	€155,53 Mengenrabatte	5 In Stock
Mounted	25.0	Stainless Steel	300	#15-397	€155,53 Mengenrabatte	2 In Stock
Mounted	25.0	Stainless Steel	400	#15-398	€155,53 Mengenrabatte	3 In Stock
Mounted	25.0	Stainless Steel	500	#12-174	€155,53 Mengenrabatte	2 In Stock
Mounted	25.0	Stainless Steel	600	#15-399	€155,53 Mengenrabatte	2 In Stock
Mounted	25.0	Stainless Steel	800	#16-739	€155,53 Mengenrabatte	2 In Stock
Mounted	25.0	Stainless Steel	1000	#12-175	€155,53 Mengenrabatte	1 In Stock



Copyright 2023 | Edmund Optics, Ltd Unit 1, Opus Avenue, Nether Poppleton, York, YO26 6BL, UK
 Telefonnr.: 1-800-363-1992 :
www.edmundoptics.com