

[Alle Produkte](#) / [Optikkomponenten](#) / [Prismen](#) / [Retroreflektoren](#)

TECHSPEC® Retroreflektoren aus N-BK7 mit Fassung



- Einfallendes Licht wird zur Lichtquelle zurückreflektiert
- Ideal für Justagearbeiten
- Gewindebohrungen 1/4"-20 zur einfachen Montage
- Auch [ungefasst](#) lieferbar

Spezifikationen

Physikalische und mechanische Eigenschaften

Toleranz Durchmesser (mm): +0.0/-0.1

Optische Eigenschaften

Oberflächenqualität: 60-40


Bildorientierung: Left-Handed

Strahlablenkung (°): 180

Passfehler, Power (Ringe) @ 632,8 nm: 0.25

Unregelmäßigkeit (Ringe) @ 632,8 nm: 0.25

Technische Informationen



Produkte

Innendurchmesser (mm)	Beschichtung	Artikelnummer	Preis	Kaufen
7.20	Silver with protective overcoat	#49-079	€278,10 Mengenrabatte	2 In Stock
7.20	VIS 0° & Silver with protective overcoat	#12-211	€304,88 Mengenrabatte	4 In Stock
7.20	NIR II & Silver with protective overcoat	#12-670	€304,88 Mengenrabatte	3 In Stock
12.70	Silver with protective overcoat	#45-203	€364,62 Mengenrabatte	20+ In Stock
12.70	VIS 0° & Silver with protective overcoat	#12-216	€391,40 Mengenrabatte	5 In Stock
12.70	NIR II & Silver with protective overcoat	#12-671	€391,40 Mengenrabatte	20+ In Stock
25.40	Silver with protective overcoat	#45-188	€406,85 Mengenrabatte	9 In Stock
25.40	VIS 0° & Silver with protective overcoat	#12-217	€423,33 Mengenrabatte	5 In Stock
25.40	NIR II & Silver with protective overcoat	#12-672	€423,33 Mengenrabatte	3 In Stock
38.10	Silver with protective overcoat	#45-190	€487,19 Mengenrabatte	4 In Stock
50.80	Silver with protective overcoat	#45-192	€566,50 Mengenrabatte	2 In Stock
63.50	Silver with protective overcoat	#49-080	€664,35 Mengenrabatte	Kontakt
76.20	Silver with protective overcoat	#49-081	€798,25 Mengenrabatte	4 In Stock



Copyright 2023 | Edmund Optics, Ltd Unit 1, Opus Avenue, Nether Poppleton, York, YO26 6BL, UK
 Telefonnr.: 1-800-363-1992 :
www.edmundoptics.com