

[Alle Produkte](#) / [Kameras](#) / [Gigabit-Ethernet-Kameras](#)

Teledyne Imaging FLIR/IIS Blackfly[®] GigE-Kameras mit PoE

Mehr Produkte von [Teledyne FLIR](#)



- Sehr kompakter Aufbau
- Maximale Flexibilität durch Power over Ethernet (PoE)
- Inklusive Bilderfassungssoftware und SDK FlyCapture2
- Versionen mit [USB3](#) ebenfalls verfügbar



Teledyne
Authorized
Distributor

Spezifikationen

Produktdetails			
Hersteller: FLIR		Kamerareihe: Blackfly®	
Physikalische und mechanische Eigenschaften			
Größe (mm):		29 x 29 x 30 (excludes connectors and lens mount)	Gehäuse: Full
Sensor			
Pufferspeicher: 16MB		Sensor: Progressive Scan CMOS	
Verschlusstyp: Global		Bildverarbeitungsstandard: GigE Vision v1.2	
Anschlussmöglichkeiten Hardware & Schnittstelle			
Schnittstelle: GigE (PoE)		Stecker: GigE, RJ45 with Screw Locks	
Stromversorgung:		GPIOs:	
Power Supply Required and Sold Separately: USA: #88-063 Europe: #88-063 Japan: #88-063 Korea: Not Available China: #88-063		1 opto-isolated input, 1 opto-isolated output	
Synchronisation: Hardware Trigger (GPIO) or Software Trigger		Orientierung des Anschlusses: Back Panel	
GPIO-Steckertyp: 6-pin Hirose (HR10)			
Gewinde & Montage			
Gewinde:		¼-20 with Tripod Mount Adapter #88-210	
Umwelt & Haltbarkeit			
Betriebstemperatur (°C): 0 to +45		Lagerungstemperatur (°C): -30 to +60	

Technische Informationen

Produkte

Typ	Modellnummer	Sensorformat	Auflösung (Megapixel)	Stecker	Mount	Artikelnummer	Preis	Kaufen
Monochrome Camera	BFLY-PGE-23S6M-C	1/1.2"	2.30	GigE, RJ45 with Screw Locks	C- Mount	#33-180	€595,00	1 In Stock
Color Camera	BFLY-PGE-23S6C-C	1/1.2"	2.30	GigE, RJ45 with Screw Locks	C- Mount	#33-181	€595,00	1 In Stock
Monochrome Camera	BFLY-PGE-12A2M-CS	1/3"	1.20	GigE, RJ45 with Screw Locks	CS- Mount	#89-533	€355,00	1 In Stock
Color Camera	BFLY-PGE-12A2C-CS	1/3"	1.20	GigE, RJ45 with Screw Locks	CS- Mount	#89-534	€355,00	Kontakt
Monochrome Camera	BFLY-PGE-13E4M-CS	1/1.8"	1.30	GigE, RJ45 with Screw Locks	CS- Mount	#88-043	€486,00	2 In Stock
Color Camera	BFLY-PGE-13E4C-CS	1/1.8"	1.30	GigE, RJ45 with Screw Locks	CS- Mount	#88-044	€486,00	1 In Stock
Monochrome Camera	BFLY-PGE-20E4M-CS	1/1.8"	2.00	GigE, RJ45 with Screw Locks	CS- Mount	#89-997	€635,00	1 In Stock
Color Camera	BFLY-PGE-20E4C-CS	1/1.8"	2.00	GigE, RJ45 with Screw Locks	CS- Mount	#89-998	€635,00	1 In Stock
Monochrome Camera	BFLY-PGE-31S4M-C	1/1.8"	3.20	GigE, RJ45 with Screw Locks	C- Mount	#34-511	€585,00	2 In Stock
Color Camera	BFLY-PGE-31S4C-C	1/1.8"	3.20	GigE, RJ45 with Screw Locks	C- Mount	#34-510	€585,00	1 In Stock

Monochrome Camera	BFLY-PGE-50S5M-C	2/3"	5.00	GigE, RJ45 with Screw Locks	C-Mount	#34-513	€920,00	2 In Stock
Color Camera	BFLY-PGE-50S5C-C	2/3"	5.00	GigE, RJ45 with Screw Locks	C-Mount	#34-512	€920,00	1 In Stock
Monochrome Camera	BFLY-PGE-50S5M-CS	2/3"	5.00	GigE, RJ45 with Screw Locks	CS-Mount	#22-073	€920,00	1 In Stock



Copyright 2023 | Edmund Optics, Ltd Unit 1, Opus Avenue, Nether Poppleton, York, YO26 6BL, UK
 Telefonnr.: 1-800-363-1992 :
www.edmundoptics.com