

Laserschutzbrille LS19, Komfortbrille, verstellbarer Steg



Adjustable Bridge Wrap Around Frame. Image represents frame style only. Filter color will vary by product specification.

Produkt #17-647 3-4 TAGE



1



€272,00

+ WARENKORB

Stk. 1-5

€272,00

Stk. 6+

€244,80

Mengenrabatte

[Angebotsanfrage](#)

⚠ Preise exklusiv der geltenden Mehrwertsteuer und Abgaben

Downloadbereich

Farbe:
Grey

Optische Dichte OD:
>5 @ 1025 - 1075nm
>6 @ 1035 - 1070nm
>7 @ 1045 - 1065nm
>2 @ 1450 - 1650nm
>3 @ 1651 - 1775nm
>4 @ 1776 - 3000nm

>5 @ 1980 - 2550nm
>5 @ 5200 - 11,000nm
>6 @ 9000 - 10,600nm

Durchlässigkeit für sichtbares Licht VLT (%):
23

Zertifizierung EN 207/208:
DIRMLB5 @ 1025 - 1075nm, DIRMLB6 @ 1035 - 1070nm, D LB6 and IR LB7 and MLB7Y @ 1045 - 1065nm, DIR LB2 @ 1450 - 1650nm, DI LB3 and R LB3Y @ 1651 - 1775nm, DI LB4 and R LB3Y @ 1776 - 3000nm & 5200 - 11,000nm

Filtermaterial:
Polymer

Filter:
LS19

Art:
Adjustable Bridge Wrap Around

Konformität mit Standards

RoHS 2015:
[Konform](#)

Konformitätszertifikat:
[Anzeigen](#)