NOTES:


1. SUBSTRATE: FUSED SILICA


2. RoHS: COMPLIANT

3. SURFACE S2 TO BE PARALLEL TO SURFACE S1 TO WITHIN < 5 ARCMIN

4. COATING (APPLY ACROSS COATING APERTURE) \$1& \$2: R(ABS) ≤1.0% FROM 350 - 450nm R(AVG) ≤1.5% FROM 250 - 700nm







FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS ARE FOR REFERENCE ONLY

	\$1	\$2				Edmund Option	2S®
SHAPE	PLANO	PLANO					
SURFACE ACCURACY	1λ	1λ	THIRD ANGLE PROJECTION		TITLE	12.5 x 12.5mm UV-VIS COATED, 1λ FUSED SILICA WINDOW	
SURFACE QUALITY	60-40	60-40					
CLEAR APERTURE	11.25 x 11.25	11.25 x 11.25		1		SIEIC/ TTITE OTT	CHEET
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED	ALL DIMS IN	mm	DWG NO	84472	SHEET 1 OF 1

