



TECHSPEC® Achromatic Lenses

Edmund Optics Inc.

USA | UK | France | Germany | Japan | Singapore | China | Korea | Italy

TECHSPEC® ACHROMATIC LENSES



32323
TUE DEC 16 2008 UNITS ARE μm .
FIELD :
RMS RADIUS : 41.566
GD RADIUS : 117.604
SCALE BAR : 400


REFERENCE : CHIEF RAY

EDMUND OPTICS
HTTP://WWW.EDMUNDOPTICS.COM

CHROMATIC FOCAL SHIFT

32323
TUE DEC 16 2008
MAXIMUM FOCAL SHIFT RANGE: 218.9467 μm
DIFFRACTION LIMITED RANGE: 9.406 μm
PUPIL ZONE: 0.0000


EDMUND OPTICS
HTTP://WWW.EDMUNDOPTICS.COM



TRANSVERSE RAY FAN PLOT

32323
TUE DEC 16 2008
MAXIMUM SCALE: $\pm 500.000 \mu\text{m}$.
0.486 0.588 0.656
SURFACE: IMAGE

EDMUND OPTICS
HTTP://WWW.EDMUNDOPTICS.COM



POLYCHROMATIC DIFFRACTION MTF

32323
TUE DEC 16 2008
DATA FOR 0.4000 TO 0.7000 μm .
SURFACE: IMAGE

EDMUND OPTICS
HTTP://WWW.EDMUNDOPTICS.COM