


NOTES:

1. SUBSTRATE
2. SURFACE S2 TO BE PARALLEL WITH SURFACE S1 TO WITHIN 5 arcsec
3. COATING (APPLY ACROSS COATING APERTURE)  
ENVIRONMENTAL DURABILITY:  
PHYSICAL DURABILITY:  
PERFORMANCE SPECIFICATIONS:  
T(avg): >85% FROM 985 - 1600nm FOR RANDOM POLARIZATION @ 45° AOI  
T(abs): >80% FROM 985 - 1600nm FOR ALL POLARIZATIONS @ 45° AOI  
R(avg): >97% FROM 715 - 900nm FOR RANDOM POLARIZATION @ 45° AOI  
R(abs): >95% FROM 715 - 900nm FOR ALL POLARIZATIONS @ 45° AOI  
T(abs): = 50% 950nm @ 45° AOI

S1: HARD COATED  
S2: SINGLE LAYER MgF2



4. FINE GRIND SURFACE

5. POWER, IRREGULARITY, AND SURFACE QUALITY SPECIFICATIONS  
APPLY ACROSS CLEAR APERTURE
6. TRANSMITTED WAVEFRONT DISTORTION RMS@ 632.8nm  $\leq \frac{1}{4} \lambda$
7. ROHS COMPLIANT





LONGPASS FILTER

**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**



SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2
SHAPE	PLANO	PLANO
SURFACE QUALITY	60-40	60-40
CLEAR APERTURE	Ø11.00	Ø11.00
COATING APERTURE	Ø11.00	Ø11.00
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED

THIRD ANGLE PROJECTION 		 <b>Edmund Optics®</b>	
TITLE		Ø12.5mm, 950nm DICHROIC LONGPASS FILTER	
ALL DIMS IN	mm	DWG NO	87027
			SHEET 1 OF 1