



NOTES:

1. SUBSTRATE: N-BK7
2. COATING (APPLY ACROSS CLEAR APERTURE)
 - S1: PROTECTED ALUMINUM
Ravg >85% @ 400 - 700nm
 - S2: UNCOATED

3. FINE GRIND SURFACE

4. RoHS COMPLIANT




**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

REV. A	S1	S2
WAVELENGTH RANGE (nm)	400 - 700	400 - 700
SURFACE QUALITY	40-20	40-20
ANGLE TOLERANCE (arcmin)	±6	±6
TYPE	SPECIALTY MIRROR	SPECIALTY MIRROR
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED

THIRD ANGLE PROJECTION



ALL DIMS IN

mm

EO® Edmund Optics®

TITLE

Ø3mm, ALUMINUM COATED, CONE LENS

DWG NO

45938

SHEET
1 OF 1