

NOTES:


1. SUBSTRATE MATERIAL:  
N-BK7

2. COATING (APPLY ACROSS CLEAR APERTURE)

S1 & S2: MgF2 (400-700nm)  
R(AVG) ≤ 1.75% @ 400 - 700nm


3. FINE GROUND SURFACE

4. RoHS COMPLIANT



**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2	EFL	12.50	 <b>Edmund Optics®</b>	12.5mm DIA X 12.5mm FL MGF2 COATED, CYLINDER LENS	
SHAPE	CONVEX	PLANO	BFL	7.57			
RADIUS	6.48	INFINITY	THIRD ANGLE PROJECTION 		TITLE		
SURFACE QUALITY	60-40	60-40					
CLEAR APERTURE	Ø11.50	Ø11.50	ALL DIMS IN		mm	DWG NO	48352
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED					