




NOTES:

- 1. SUBSTRATE MATERIAL:
Fused Silica
- 2. COATING:
S1 & S2: NONE
- 3. EXTINCTION RATIO:
>100:1 @ 300 - 400nm (Typical)
>50,000:1 @ 450 - 550nm (Typical)
>800:1 @ 700 - 1400nm (Typical)
>1000:1 @ 1400 - 2650nm (Typical)
- 4. ANGLE OF INCIDENCE: ±40°
- 5. OPERATING TEMPERATURE (°C): -50 to 80
- 6. WAVELENGTH RANGE (nm): 300 - 2700
- 7. RoHS COMPLIANT



SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY



THIRD ANGLE PROJECTION 		TITLE	Ø25.4mm, 300 - 2700nm BROADBAND POLARIZER		
ALL DIMS IN	mm	DWG NO	89602	SHEET 1 OF 1	

**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**