NOTES:

- SUBSTRATE: GRADE A FINE ANNEALED 1. SCHOTT: N-BK7 517/642
- 2. **ROHS COMPLIANT**
- SURFACE \$2 TO BE PARALLEL TO SURFACE \$1 TO WITHIN 3 3. ARCMIN
- COATING (APPLY ACROSS COATING APERTURE) SPECIFICATIONS AT 45° AOI AND RANDOM POLARIZATION 4.

 $R(abs) = 50\% \pm 5\% @ 550nm$

 $R(abs) = 50\% \pm 10\%$ FROM 400-700nm

 $T(abs) = 50\% \pm 5\% @ 550nm$

 $T(abs) = 50\% \pm 10\%$ FROM 400-700nm

VISUÁL COLOR = NEUTRAL

S2: BBAR


R(abs) ≤ 2.0% FROM 400-700nm R(avg) ≤ 1.0% FROM 400-700nm

∕5.∖

FINE GRIND SURFACE



MARK IDENTIFIES BEAMSPLITTER SURFACE



PARTS TO THIS DRAWING

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2	
SHAPE	PLANO	PLANO	
SURFACE FLATNESS	1λ PER 25mm	1λ PER 25mm	
SURFACE QUALITY	60 - 40	60 - 40	
MIN CLEAR APERTURE	63.75 x 63.75	63.75 x 63.75	
MIN COATING APERTURE	PERTURE 63.75 x 63.75 63.75		
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED	

		Edmund Optics ®		
THIRD ANG PROJECTIC		TITLE	BS VIS 50R/50T 75X75MM 1MM THK	
ALL DIMS IN	mm	DWG NO	35948	SHEET 1 OF 1