## NOTES:

- 1. SUBSTRATE MATERIAL: N-BK7
- 2. BEAM DEVIATION: ±3 arcmin
- 3. COATING (APPLY ACROSS CLEAR APERTURE)


\$1, \$2, \$3 & \$4: R(abs) <0.25% @ 780nm \$5: Tp/Ts >1000:1 @ 780nm TRANSMISSION >95% REFLECTION >99.5%

4. FINE GROUND SURFACE

5. ELEMENTS TO BE CEMENTED WITH NORLAND OPTICAL ADHESIVE 61

6. PROTECTIVE BEVEL AS NEEDED

7. MARK IDENTIFIES BEAMSPLITTER COATING RIGHT ANGLE PRISM



## FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS ARE FOR REFERENCE ONLY

			_			Edmund ()ntid	C®
	\$1, \$2, \$3, \$4	\$5				Edmund Option	JO
SHAPE	PLANO	PLANO	THIRD ANGLE PROJECTION		TITLE	15mm, 780nm, LASER LINE POLARIZING CUBE BEAMSPLITTER	
SURFACE FLATNESS	λ/4	λ/4					
SURFACE QUALITY	40-20	40-20		1		BEF WHO! EITTER	CHEET
CLEAR APERTURE	90	90	ALL DIMS IN	mm	DWG NO	47047	SHEET 1 OF 1