NOTES:

1. SUBSTRATE MATERIAL: N-BK7

2. SURFACE S2 TO BE PARALLEL WITH SURFACE S1 TO WITHIN ≤ 3ARCMIN


3. COATING (APPLY ACROSS CLEAR APERTURE)


S1: 40% R ±5% @ 550nm 60% T ±5% @ 550nm

S2: AR R(avg) ≤1%, R(abs) ≤2% @ 400 - 700nm

4. FINE GROUND SURFACE

5. ROHS COMPLIANT





FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS ARE FOR REFERENCE ONLY

 \square

REV. A	S1	\$2			Edmund Optic	CS®
SHAPE	PLANO	PLANO				
ANGLE OF INCIDENCE	45°	45°	THIRD ANGLE	TITLE	12.5 x 17.5mm, 40 R/60 T, PLATE BEAMSPLITTER	
SURFACE QUALITY	60-40	60-40				0.1557
SURFACE FLATNESS	1λ PER 25mm	1λ PER 25mm	ALL DIMS IN mm	DWG NO	68383	SHEET 1 OF 1