



FOCAL LENGTH (EFL): 80 ± 0,8  
 BACK FOCAL LENGTH (BFL): 77,33

1 AR COATING: NONE

LEFT SURFACE		MATERIAL	RIGHT SURFACE	
R	82,29±0,082 CX	GLASS N-K5 523/595	R	82,29±0,082 CX
Øe	39		Øe	39
3/	3 (0,5) λ=632,8 nm		3/	3 (0,5) λ=632,8 nm
4/	-		4/	1,91'
5/	40 - 20 (MIL-PRF-13830B)		5/	40 - 20 (MIL-PRF-13830B)
6/	-		6/	-

PROTECTIVE CHAMFERS AS NEEDED		FIRST ANGLE PROJECTION	<b>Edmund Optics®</b>		
ROHS: COMPLIANT	SCALE: NONE λ = 587,6nm				
SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY			TITLE	40mm Dia, x 80mm FL Uncoated, DCX N-K5 Lens	
FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING			ALL DIMS IN:	DWG NO	32906
INDICATIONS IN ACCORDANCE WITH ISO 10110		mm			SHEET 1 OF 1