
## NOTES:


- 1. SUBSTRATE: ZnSe
- 2. SURFACE S2 TO BE PARALLEL TO SURFACE S1 TO WITHIN < 3 ARCMIN
- 3. COATING (APPLY ACROSS COATING APERTURE)

\$1& \$2: HIGH- EFFICIENCY BROADBAND (BBAR)  $R(AVG) \le 0.5\%$  FROM 8 -  $12\mu m$ 



5. RoHS: COMPLIANT





## PARTS TO THIS DRAWING

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS ARE FOR REFERENCE ONLY

SHAPE	S1 PLANO	\$2 PLANO				Edmund Option	CS®
SURFACE QUALITY	40-20	40-20		1		25 Amm DIA v 2mm THICK 9 12um CO	ATED
SURFACE FLATNESS @ 10.6µm	λ/20	λ/20	THIRD ANGLE PROJECTION		TITLE	25.4mm DIA x 2mm THICK 8 - 12µm COATED ZnSe WINDOW	
CLEAR APERTURE	Ø22.86	Ø22.86				ZIBC WINDOW	CHEET
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED	ALL DIMS IN	mm	DWG NO	39434	SHEET 1 OF 1

