

NOTES:

- 1. SUBSTRATE: UV GRADE FUSED SILICA
- 2. COATING (APPLY ACROSS COATING APERTURE): \$1 & \$2: NIR I (600-1050nm) R(AVG) ≤0.5% @ 600 - 1050nm
- 3. SURFACE S2 TO BE PARALLEL TO SURFACE S1 TO WITHIN <5 ARCSEC

4. FINE GRIND SURFACE

5. ROHS COMPLIANT





FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS ARE FOR REFERENCE ONLY

	\$1	\$2]			Edmund Opt	ICS®
SHAPE	PLANO	PLANO	THIRD ANGLE PROJECTION		TITLE	25mm Dia., 2mm Thick, NIR I Coated λ/10 Fused Silica Window	
SURFACE QUALITY	20-10	20-10					
CLEAR APERTURE	Ø20.00	Ø20.00					CLIEFT
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED	ALL DIMS IN	mm	DWG NO	11892	SHEET 1 OF 1