



FOCAL LENGTH (EFL):  $-25 \pm 0,25$   
 BACK FOCAL LENGTH (BFL):  $-26,96$

1 AR COATING: NONE

LEFT SURFACE		MATERIAL	RIGHT SURFACE	
R	$19,62 \pm 0,02 \text{ CV}$	GLASS N-SF11 785/258	R	$\infty \text{ PL}$
$\phi e$	24		$\phi e$	24
3/	3 (0,5) $\lambda=632,8 \text{ nm}$		3/	3 (0,5) $\lambda=632,8 \text{ nm}$
4/	-		4/	1,27'
5/	40 - 20 (MIL-PRF-13830B)		5/	40 - 20 (MIL-PRF-13830B)
6/	-		6/	-

PROTECTIVE CHAMFERS AS NEEDED

ROHS: COMPLIANT  
 SCALE: NONE  
 $\lambda = 587,6 \text{ nm}$

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY

FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING

INDICATIONS IN ACCORDANCE WITH ISO 10110

FIRST ANGLE PROJECTION



ALL DIMS IN: mm

**EO**® Edmund Optics®

TITLE 25,0mm Dia, x -25 FL, Uncoated, Plano-Concave Lens

DWG NO 45030

SHEET SIZE A4  
 SHEET 1 OF 1