




FOCAL LENGTH (EFL):  $-6 \pm 0,06$   
 BACK FOCAL LENGTH (BFL):  $-6,56$

1 AR COATING: NONE

| LEFT SURFACE |                            | MATERIAL             | RIGHT SURFACE |                            |
|--------------|----------------------------|----------------------|---------------|----------------------------|
| R            | $4,71 \pm 0,005$ CV        | GLASS N-SF11 785/258 | R             | $\infty$ PL                |
| Øe           | 2,5                        |                      | Øe            | 2,5                        |
| 3/           | 3 (0,5) $\lambda=632,8$ nm |                      | 3/            | 3 (0,5) $\lambda=632,8$ nm |
| 4/           | -                          |                      | 4/            | 3,82'                      |
| 5/           | 20 - 10 (MIL-PRF-13830B)   |                      | 5/            | 20 - 10 (MIL-PRF-13830B)   |
| 6/           | -                          |                      | 6/            | -                          |

PROTECTIVE CHAMFERS AS NEEDED

ROHS: COMPLIANT  
 SCALE: NONE  
 $\lambda = 587,6$  nm

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY

FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING

INDICATIONS IN ACCORDANCE WITH ISO 10110

FIRST ANGLE PROJECTION



ALL DIMS IN: mm

**EO**® Edmund Optics®

TITLE 3,0mm Dia, x -6 FL, Uncoated, Plano-Concave Lens

DWG NO 45374

SHEET SIZE A4  
 SHEET 1 OF 1