






FOCAL LENGTH (EFL): 24 ±0,24
 BACK FOCAL LENGTH (BFL): 22,63

1 AR COATING: NONE

LEFT SURFACE		MATERIAL	RIGHT SURFACE	
R	11,003±0,011 CX	GLASS FUSED SILICA 458/678	R	∞ PL
Øe	5,4		Øe	5,4
3/	2 (0,2) λ=632,8 nm		3/	2 (0,2) λ=632,8 nm
4/	-		4/	2,18'
5/	20 - 10 (MIL-PRF-13830B)		5/	20 - 10 (MIL-PRF-13830B)
6/	-		6/	-

PROTECTIVE CHAMFERS AS NEEDED			FIRST ANGLE PROJECTION 		 Edmund Optics®			
ROHS: COMPLIANT	SCALE: NONE	λ = 587,6nm						
SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY					TITLE	6mm Diameter x 24mm FL, 266nm Coated, Laser Grade PCX Lens		
FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING					DWG NO	87930	SHEET SIZE A4	SHEET 1 OF 1
INDICATIONS IN ACCORDANCE WITH ISO 10110			ALL DIMS IN:	mm				