NOTES:

2.

- 1. SUBSTRATE:
 - PARTS TO THIS DRAWING SAPPHIRE (AL2O3)
- 3. COATING (APPLY ACROSS CLEAR APERTURE)


SURFACE S2 TO BE PARALLEL WITH SURFACE S1 TO WITHIN ≤ 3.5 ARCMIN


S1 & S2: R(AVG) ≤0.25% @ 880nm R(AVG) ≤1.25% @ 400 - 870nm R(AVG) ≤1.25% @ 890 - 1000nm



FINE GRIND SURFACE

ROHS COMPLIANT





SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS ARE FOR REFERENCE ONLY

	\$1	\$2		
SHAPE	PLANO	PLANO		
CLEAR APERTURE	Ø18.00	Ø18.00		
SURFACE FLATNESS	2λ	2λ		
SURFACE QUALITY	80-50	80-50		
BIREFRINGENCE (no-ne)	0.008	0.008		
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED		

				Edmund Optics®	
	THIRD ANGLE PROJECTION	\$	TITLE	20mm Dia., 1mm Thick, VIS-NIR AR Coated Sapphire Window	
_	ALL DIMS IN	mm	DWG NO	20798	SHEET 1 OF 1