NOTES:

1. SUBSTRATE: SAPPHIRE (AL2O3) DO NOT MANUFACTURE PARTS TO THIS DRAWING


- 2. SURFACE S2 TO BE PARALLEL WITH SURFACE S1 TO WITHIN ≤ 3.5 ARCMIN
- 3. COATING (APPLY ACROSS CLEAR APERTURE)


S1 & S2: R(AVG) <1.5% @ 2000-5000nm R(ABS) <3.0% @ 2000-5000nm R(AVG) <1.75% @ 2000-4000nm



FINE GRIND SURFACE

5. ROHS COMPLIANT





SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS ARE FOR REFERENCE ONLY

	\$1	\$2		
SHAPE	PLANO	PLANO		
CLEAR APERTURE	Ø18.00	Ø18.00		
SURFACE FLATNESS	2λ	2λ		
SURFACE QUALITY	80-50	80-50		
BIREFRINGENCE (n _o -n _e)	0.008	0.008		
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED		

		Edmund Optics®		
THIRD ANGLE PROJECTION	\rightarrow	TITLE	20mm Dia., 1mm Thick, BBAR (2000-5000nm) AR Coated Sapphire Window	
ALL DIMS IN	mm	DWG NO	21023	SHEET 1 OF 1