




FOCAL LENGTH (EFL): 200 ±2

BACK FOCAL LENGTH (BFL): 197,89



LEFT SURFACE AR COATING:

YAG-BBAR

R(ABS) < 0,25% @ 532nm @ 0° AOI

R(ABS) < 0,25% @ 1064nm @ 0° AOI

R(AVG) < 1,0% FROM 500-1100nm @ 0° AOI

RIGHT SURFACE AR COATING:

YAG-BBAR

R(ABS) < 0,25% @ 532nm @ 0° AOI

R(ABS) < 0,25% @ 1064nm @ 0° AOI

R(AVG) < 1,0% FROM 500-1100nm @ 0° AOI

LEFT SURFACE		MATERIAL	RIGHT SURFACE	
R	103,36 CX	GLASS N-BK7 Nd: 1,517 Vd: 64,2	R	∞ PL
Øe	14		Øe	14
3/	3 (0,5) λ=632,8 nm		3/	3 (0,5) λ=632,8 nm
4/	-		4/	1,93'
5/	40 - 20		5/	40 - 20
6/	-		6/	-


PROTECTIVE CHAMFERS AS NEEDED

ROHS:
COMPLIANT

SCALE:
NONE

λ = 587,6nm

FIRST ANGLE
PROJECTION



SPECIFICATIONS SUBJECT TO CHANGE WITHOUT
NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY

FOR INFORMATION ONLY: DO NOT MANUFACTURE
PARTS TO THIS DRAWING

INDICATIONS IN ACCORDANCE WITH ISO 10110

ALL DIMS
IN:

mm



Edmund Optics®

TITLE

15mm Dia x 200mm FL, YAG-BBAR
Coated, Plano-Convex Lens

DWG NO

14381

SHEET
SIZE A4

SHEET
1 OF 1