


# TECHSPEC® CANOPUS™ REFLECTIVE BEAM EXPANDERS

250-700nm • 3X #37-186

- Broadband Performance for UV, Visible, and IR Applications from 250nm to 10µm
- $\lambda/10$  or  $\lambda/8$  Wavefront Error
- Easy Mounting with Integrated Alignment Features
- Patent Pending



TECHSPEC® Canopus™ Reflective Beam Expanders are ideal for applications requiring broadband or achromatic beam expansion and a wide variety of light sources. The all-reflective design enables these beam expanders to be used with a variety of lasers including tunable, ultraviolet, and ultrafast sources, while the innovative design ensures high precision with minimal wavefront distortion. A variety of integrated design elements, including reflective flats, thread holes and thru-holes, simplify alignment, mounting, and integration into any laser application. The monolithic design ensures performance and stability independent of changes in temperature.

For more information on beam expanders and their application, please see online for our Technical Resource: [Application Note on Beam Expanders](#)

<b>Wavelength Range:</b>	250-700nm
<b>Expansion Power:</b>	3X
<b>Entrance Aperture:</b>	4mm
<b>Exit Aperture:</b>	12mm
<b>Wavefront Error, P-V:</b>	$\lambda/10$ @ 633nm @ 1mm Input Beam
<b>Substrate:</b>	Aluminum 6061-T6
<b>Length:</b>	72.6mm
<b>Width:</b>	38.1mm
<b>Height:</b>	25.4mm
<b>Weight:</b>	117g
<b>Coating:</b>	Enhanced Aluminum (250-700nm)
<b>Coating Specification:</b>	$R_{avg} > 89\%$ @ 250 - 450nm $R_{avg} > 85\%$ @ 250 - 700nm
<b>Angle of Incidence:</b>	0°
<b>Surface Roughness:</b>	<50 RMS Å
<b>Surface Quality:</b>	40-20

