

NOTES:

1. SUBSTRATE:

Sapphire (Al₂O₃)


2. SURFACE S2 TO BE PARALLEL WITH SURFACE S1 TO WITHIN ≤3.5 ARCMIN

3. COATING (APPLY ACROSS CLEAR APERTURE)

S1&S2: Ravg ≤0.25% @ 880nm
Ravg ≤1.25% @ 400 - 870nm
Ravg ≤1.25% @ 890 - 1000nm

4. FINE GRIND SURFACE

5. ROHS COMPLIANT




**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2
SHAPE	PLANO	PLANO
CLEAR APERTURE	Ø 135.00	Ø 135.00
SURFACE FLATNESS	2 - 4λ (typical)	2 - 4λ (typical)
SURFACE QUALITY	80-50	80-50
BIREFRINGENCE	0.008	0.008
BEVEL	PROTECTED AS NEEDED	PROTECTED AS NEEDED

THIRD ANGLE
PROJECTION



ALL DIMS IN

mm



Edmund Optics®

TITLE

150mm Dia., 2mm Thick, VIS-NIR AR Coated,
Sapphire Window

DWG NO

24174

SHEET
3 OF 3