




FOCAL LENGTH (EFL): $35 \pm 0,35$
 BACK FOCAL LENGTH (BFL): $32,3$

- 1 532nm Laser AR Coating
 $R(\text{ABS}) < 0,25\% @ 532\text{nm} @ 0^\circ \text{AOI}$

LEFT SURFACE		MATERIAL	RIGHT SURFACE	
R 16,663 CX Øe 11,7 (λ) SEE NOTE 1 3/ 2 (0,2) λ=632,8 nm 4/ - 5/ 10 - 5 6/ 10J-cm ⁻² ; 532nm; 20ns [20Hz]		GLASS Fused Silica 458/678	R ∞ PL Øe 11,7 (λ) SEE NOTE 1 3/ 2 (0,2) λ=632,8 nm 4/ 2,18' 5/ 10 - 5 6/ 10J-cm ⁻² ; 532nm; 20ns [20Hz]	
PROTECTIVE CHAMFERS AS NEEDED ROHS: COMPLIANT SCALE: NONE λ = 355nm SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING INDICATIONS IN ACCORDANCE WITH ISO 10110		FIRST ANGLE PROJECTION 	Edmund Optics® TITLE 12,7mm Dia x 35mm FL, 532nm Laser AR Coating, 10J Coated, Plano-Convex Lens DWG NO 38708 SHEET SIZE A4 SHEET 1 OF 1	