



Exemplar® LS

Low Straylight Smart CCD Spectrometer



The Exemplar® LS is a smart CCD spectrometer optimized for low straylight by utilizing an unfolded Czerny-Turner spectrograph. It features on board data processing, USB 3.0 communication, and temperature compensation. The Exemplar LS is also optimized for multi-channel operation, featuring ultra-low trigger delay and gate jitter. Additionally, the Exemplar LS features a 2048 element detector and built-in 16-bit digitizer with greater than 2.0 MHz readout speed.

The Exemplar LS is available in two standard spectral configurations: 200nm - 400nm and 200nm - 850nm with resolutions of less than 0.4nm. Custom configurations are available for OEM applications.

Applications:

- UV, Vis, and NIR: Spectroscopy / Spectroradiometry / Spectrophotometry
- **Absorbance / Reflectance / Transmittance**
- **Kinetic Reaction Monitoring**
- **Transient Spectral Analysis**
- **Wavelength Identification**
- **OEM Systems Integration**
- **Multi-point Sampling**

Additional Features:

- Temperature Compensation for Ultra-low Thermal Drift
- 1ms Minimum Integration Time
- Low Straylight Spectrograph
- < 0.4nm Spectral Resolution
- >2.0 MHz Readout Speed
- UV Vis (200nm 850nm)



SMART:

On-board processing including averaging, smoothing, and dark compensation

SPEED:

"SuperSpeed" USB 3.0 transferring up to 900 spectra per second

SYNCHRONOUS:

Supports up to 32 devices with ultra-low trigger delay (14ns) & gate jitter (+/- 1ns)


SIGNAL TO NOISE RATIO:				
On-board Averaging 1	~295			
On-board Averaging 10	~929			
On-board Averaging 100	~2450			

	28 0 € 280 €	☑ 2000	₽ ABCD	₩ ZABN	₩ PLM	ZBUZ	V ===	ZUVE	
	2.6297 ms	2.5651 ms	16.3336 m		10.6829 ms	3.8156 ms	2.5428 ms	2.2358 ms	
Back	Samo.	▼ Strid	≥ 200	₩ ZDMS	₹ ZOUH	₩ ZDUI	V	☑ ZDUA	
	2.4961 ms	10.3991 ms	4.1162 ms	3.2348 ms	3.5359 ms	4.6215 ms	4.2151 ms	4.8341 ms	
Acquire	10000 10000 5000 0	284Y	1500	15000 + 10000 + 10000 + 10000 + 10000 + 10000 + 10000 + 10000 + 10000 + 10000 + 10000 + 10000 + 10000 + 10000 + 10000 + 1000000 + 100000 + 100000 + 100000 + 100000 + 100000 + 100000 + 1000000 + 100000 + 100000 + 100000 + 100000 + 100000 + 100000 + 1000000 + 1000000 + 1000000 + 1000000 + 1000000 + 1000000 + 1000000 + 1000000 + 10000000 + 10000000 + 10000000 + 100000000	1000 1500	20000 15000 10000 5000	800 1000	1500 2000	5000 5000 15000
Stop	8000 +	Mavelength PLM		8000 + 6000 +	euz	6000 -	ZBVA	ngth	ZBVE 0000 +
Save	2000		×	500 1	000 1500 20 prelength	2000 -	500 1000 Wavelet	1500 2000 rgth	0000 1000 1500 1500 1500 1500 1500
Reset	10000 +	ZBND	00	8000 + 4000 + 2000 - 500	1000 1500 1000 1500	6000 - 4000 - 2000 - 0	ECC 1000 Wasslet		20MS 6000 2000 0 500 1000 1900 200 Wavefergth
	8000 T 8000 T 4000 T	ZDUH		10000 +	100	10000	ZDMR		20UA 10000 + 5000 +
ENTERNA PARTE	2000	100 1000 1 Wassissoft	500	900	1000 1500 (evalengt)	0	500 to	1900	500 1000 1500 201 Wavelength



Power Input	USB @ < 0.5 Amps
Detector Type	Response Enhanced Linear CCD Array
Wavelength Range	200nm - 850nm
Detector Pixel Format	2048 x 1 Elements @ 14μm x 200μm Per Element
Spectrograph f/#	3.6
Spectrograph Optical Layout	Czerny-Turner
Dynamic Range	1300:1 Single Acquisition
Digitizer Resolution	16-bit or 65,535:1
Readout Speed	>2.0 MHz
Data Transfer Speed	Up to 900 Spectra per Second in Burst Mode
Trigger Delay	~14ns
Minimum Integration Time	1ms, Adjustable in 1µs Increments
Thermal Drift	~29 Counts/°C (Max)
Aux Port	External Trigger, Digital IOs & Analog IOs
Operating Temperature	5°C - 35°C
Operational Relative Humidity	85% Noncondensing
Weight	~ 0.8 lbs (0.37 kg)
Dimensions	4.9in x 3.6in x 1.4in (124mm x 91mm x 35mm)
Computer Interface	USB 3.0 / 2.0 / 1.1
Operating Systems	Windows: XP, Vista, 7 (32-bit & 64-bit)

Spectrograph



Accessories:

- Inline Filter Holders
- Fiber Optic Probes
- Fiber Patch Cords
- Cuvette Holders
- Light Sources

Entrance Slit


Slit Option	Dimensions	Approx. Resolution 200-400nm		
10μm	10μm wide x 1mm high	~0.4nm		
25μm	25μm wide x 1mm high	~0.6nm		
50μm	50μm wide x 1mm high	~1.0nm		
100μm	100μm wide x 1mm high	~1.6nm		
200μm	200μm wide x 1mm high	~3.0nm		
Custom Slit Widths Available				

Diffraction Grating

Best Efficiency	Spectral Coverage (nm)	Grating		
UV	200 - 400	1800/250		
UV - NIR	200 - 850	600/250		
Custom Configurations Available				

Software:

BWSpecTM is a spectral data acquisition software with a wide range of tools that are designed to perform complex measurements and calculations at the click of a button. It allows the user to choose between multiple data formats and offers optimization of scanning parameters, such as integration time. In addition to powerful data acquisition and data processing, other features include automatic dark removal, spectrum smoothing, and manual/auto baseline correction.





19 Shea Way, Newark, DE 19713 • Tel: (302) 368-7824 • Fax: (302) 368-7830 • Web: www.bwtek.com