



NOTES:


1. SUBSTRATE: FUSED SILICA
2. BEAM MODE: SM OR MM
3. OVERALL EFFICIENCY: 76%
4. FULL ANGLE(°): 5.94
5. COATING:
Laser V-Coat (532nm)
6. BEAM SPECIFICATION:
MINIMUM BEAM DIAMETER: 1mm
OUTPUT SHAPE: ROUND



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

EO® Edmund Optics®

	S1	S2	THIRD ANGLE PROJECTION 		TITLE	532nm, 15 x 15mm, ROUND OUTPUT, HIGH HOMOGENEITY DIFFRACTIVE DIFFUSER	
SHAPE	PLANO	PLANO	ALL DIMS IN	mm	DWG NO	14683	SHEET 1 OF 1
MIN CLEAR APERTURE	Ø13.50 x 13.50	Ø13.50 x 13.50					
BEVEL MAX FACE	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED					