


NOTES:


- 1. SUBSTRATE:
Germanium (Ge)
- 2. CENTERING TOLERANCE:
<3 ARCMIN
- 3. COATING (APPLY ACROSS CLEAR APERTURE)
S1 & S2: NONE
- 4. FINE GRIND SURFACE
- 5. FOCAL LENGTH TOLERANCE: ±2%
- 6. ROHS COMPLIANT

4. FINE GRIND SURFACE



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

			EFL @ 10.6μm	200.0	DIMENSIONS ARE FOR REFERENCE ONLY		
SHAPE	S1 CONVEX	S2 PLANO	BFL @ 10.6μm	198.05	 Edmund Optics®		
RADIUS	597.16	INFINITY					
IRREGULARITY AT 10.6μm	λ/20	λ/20			TITLE	50.8mm Dia. x 200mm FL, Uncoated, ISP Optics Germanium (Ge) PCX Lens	
SURFACE QUALITY	60-40	60-40					
CLEAR APERTURE	ø45.72	ø45.72			DWG NO	24863	
BEVEL	PROTECTED AS NEEDED	PROTECTED AS NEEDED	ALL DIMS IN	mm			
					SHEET 1 OF 1		