


NOTES:



- 1. SUBSTRATE:
M-BACD5N
- 2. NUMERICAL APERTURE: 0.55
- 3. COATING: BBAR (760 - 800nm)
S1& S2: R(AVG) <1.5% @ 760 - 800nm (Theoretical per Surface)
- 4. WORKING DISTANCE (mm): 1.20 (not including cover glass)
- 5. COVER GLASS THICKNESS (mm): 1.20
- 6. TRANSMITTED WAVEFRONT ERROR, RMS @ 632.8nm: 0.049λ
- 7. TRANSMITTED WAVEFRONT ERROR, RMS: 0.04λ @ 780nm
- 8. CLEAR APERTURE (mm): 3.75



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2
SHAPE	CONVEX	PLANO
BEVEL	PROTECTED AS NEEDED	PROTECTED AS NEEDED

EFL	3.00	 Edmund Optics®		
THIRD ANGLE PROJECTION		TITLE	0.50 NA, 3.0mm FL, HOYA Molded Glass Aspheric Lens	
ALL DIMS IN	mm	DWG NO	13589	SHEET 1 OF 1