





f' : $-13,5 \pm 0,14$

BACK FOCAL LENGTH (BFL): $-14,89$



LEFT SURFACE			MATERIAL	RIGHT SURFACE		
R 6,2 CV Øe 8,1 λ AR Rave(250nm - 700nm, 0°) ≤ 1,50% R(350nm - 450nm, 0°) ≤ 1,00% 3/ 3 (0,5) λ=632,8 nm 4/ 2,18' 5/ 40 - 20 6/ - P			GLASS Fused Silica 458/678 Nd: 1,458	R ∞ PL Øe 8,1 λ AR Rave(250nm - 700nm, 0°) ≤ 1,50% R(350nm - 450nm, 0°) ≤ 1,00% 3/ 3 (0,5) λ=632,8 nm 4/ - 5/ 40 - 20 6/ - P		
PROTECTIVE CHAMFERS AS NEEDED ROHS: COMPLIANT SCALE: NONE λ = 587,6nm SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING INDICATIONS IN ACCORDANCE WITH ISO 10110				FIRST ANGLE PROJECTION	EO Edmund Optics®	
			TITLE	9mm Dia x -13,5mm FL, UV-VIS Coated, Plano-Concave Lens		
			DWG NO	71094	SHEET SIZE	A4
			ALL DIMS IN:	mm	SHEET 1 OF 1	