

NOTES:



1. SUBSTRATE:
S-LAH64
2. CENTERING TOLERANCE (AT 587.6nm):
BEAM DEVIATION (HALF ANGLE): <3 arcmin
3. COATING (APPLY ACROSS COATING APERTURE)
S1: VIS (350-700nm)
Ravg < 0.5% @ 350 - 700nm @ ±30° AOI
Rabs < 1.5% @ 350 - 700nm @ ±30° AOI
S2: VIS (350-700nm)
Ravg < 0.5% @ 350 - 700nm @ ±30° AOI
Rabs < 1.5% @ 350 - 700nm @ ±30° AOI

4. EDGES: FINE GROUND

5. ASPHERIC FIGURE ERROR: 0.75 μm RMS

6. ASPHERIC SURFACE DESCRIBED BY (REF. COEFFICIENT TABLE):



$$Z_{ASPH}(Y) = \frac{(1/RADIUS) * Y^2}{1 + \sqrt{1 - (1+k) * (1/RADIUS)^2 * Y^2}} + D * Y^2 + E * Y^4 + F * Y^6 + G * Y^8 + H * Y^{10} + J * Y^{12} + L * Y^{14}$$



SECTION A-A

COEFFICIENT TABLE 6.

| COEFFICIENT | S1 |
|---------------|----------------|
| SEMI-DIAMETER | 1.250000E+01 |
| (1/RADIUS) | 6.43500644E-02 |
| k | -1.005000E+00 |
| D | 0.000000E+00 |
| E | 1.212640E-05 |
| F | -2.868960E-09 |
| G | 1.841910E-11 |
| H | -2.151280E-14 |
| J | 6.211730E-17 |
| L | 0.000000E+00 |

| | S1 | S2 |  Edmund Optics® | | | |
|-----------------|----------------------|----------------------|--|-------|--------------|--|
| SHAPE | CONVEX | PLANO | BFL @ 780nm: 15.73 | | | |
| RADIUS | 15.540 | INFINITY |  | | | |
| SURFACE QUALITY | 40-20 | 40-20 | | | | |
| CLEAR APERTURE | 22.5 mm | 22.5 mm | TITLE | | | |
| BEVEL | PROTECTIVE AS NEEDED | PROTECTIVE AS NEEDED | 25mm Dia., 0.63 NA, 350-700nm Coated, NIR Aspheric Lens | | | |
| ALL DIMS IN mm | | | DWG NO | 16272 | SHEET 1 OF 1 | |